

Product Information VITOKORK Abstandhalter PLUS (Spacer Pads PLUS)

Description VITOKORK Abstandhalter PLUS consist of agglomerated composition cork, equipped side with a pressure sensitive acrylic adhesive on one side.

Application The product is used as spacer pads on different materials.
E.g. on glass and on grounded, unpainted metallic surfaces.

Product Properties – Not for specification use											
carrier	granulated cork with polyurethane binder										
adhesive	acrylic adhesive										
colour	nature										
liner	siliconized paper, white										
density (DIN EN ISO 845)	approx. 190 kg/m ³										
compressive strength at (DIN EN ISO 3386)	<table border="0"> <tr> <td>10 % deformation</td> <td>approx. 30 N/cm²</td> </tr> <tr> <td>20 %</td> <td>50 N/cm²</td> </tr> <tr> <td>30 %</td> <td>70 N/cm²</td> </tr> <tr> <td>40 %</td> <td>90 N/cm²</td> </tr> <tr> <td>50 %</td> <td>110 N/cm²</td> </tr> </table>	10 % deformation	approx. 30 N/cm ²	20 %	50 N/cm ²	30 %	70 N/cm ²	40 %	90 N/cm ²	50 %	110 N/cm ²
10 % deformation	approx. 30 N/cm ²										
20 %	50 N/cm ²										
30 %	70 N/cm ²										
40 %	90 N/cm ²										
50 %	110 N/cm ²										

Processing The most important processing parameters and information on cleaning are listed in our Information on Processing Adhesive Tapes.

Storage and Shelf Live 12 month after receipt of goods, when stored at +18 °C and 60 % relative humidity out of direct sunlight, in original packaging

Special Information

All data and technical information presented are based on laboratory tests or have been compiled from supplier information to the best of our knowledge. A guarantee that the values are complete and correct can however not be given. You are kindly requested to conduct your own tests to determine the suitability of our product for your applications. Our General Conditions answer any questions on guarantees and liabilities for these products insofar as no other legal regulations apply. 01/2011 Fi